

70% Trade Specific Denatured Alcohol (TSDA-7) Mixed With 30% Demineralised Water For Injection (WFI). The water is produced by reverse osmosis and further treated using twin resin chambers, ultra-violet irradiation and 0.45 and 0.2 micron filtration.

Application

- Surface Cleaning
- General Disinfection
- Cleaning Printed Circuit Boards
- Removal of Most Inks, Paints, Fluxes, Light Oils & Greases

Features

- 70% TSDA-7
- 30% WFI Quality DI Water
- Non-Ozone Depleting
- Does Not Contain Denaturant
- Plastic-Safe
- Non-Abrasive
- Rapid-Evaporation Leaving Extremely Low Residue
- Dissolves Majority of Workplace Soils

Attribute	Specification
Appearance	Clear, colourless liquid
Odour	Ethanol
Specific Gravity (at 20°C)	0.880 - 0.888
Refractive Index (at 20°C)	1.360 - 1.370
рН	5.0 - 9.0
Acidity (ml 0.02N NaOH to pH 8.5)	< 1ml / 100ml
% Denatured Ethanol	70% v/v complies with British / US Pharmacopoeia
Non-Volatile Residues	< 50 ppm
WFI Endotoxin	< 0.25 EU / ml
WFI Total Organic Carbons	< 500 ppb
WFI Bioburden	< 10 cfu / 100ml



Ramco Facility Church Road South, Skegness, Lincolnshire PE25 3RS Telephone: +44 (0)1754 880232 Email: paulfaunt@aquazero.com **www.aquazero.com**